

Female connector M23, 12-pin, CW

Article number: 10164705

Overview

- Connector M23: 12-pin, female, clockwise (CW). Suitable for cable connection to flange connector M23 (12-pin, male, counter-clockwise (CCW)).
- EMC version
- Temperature range -40...+100 °C



Technical data

Technical data

Core cross-section	Max. 1 mm ²
Cable entry	Solder

Technical data

Cable entry	ø5...10 mm
Operating temperature	-40...+100 °C

Dimensions

connector M23,
bush contacts,
straight, 12-pin,
clockwise (CW)

