

Overview

- USB 3.0 interface cable
- screw lock Micro-B connector to type A (optional screw lock) connector, both connectors with die-cast housing
- length 3.0 m



Picture similar

Technical data

Electrical data

Number of poles	9
Connectors	USB 3.0 Micro-B connector, screw lock, die-cast housing USB 3.0 type A connector, optional screw lock, die-cast housing

Mechanical data

Smallest bending radius static	62 mm
Use in cable carriers	no

Mechanical data

Cable length [m]	3 m
Weight	≤ 150 g
Material	PVC

Interface

Data interface	USB 3.0
----------------	---------

Environmental conditions

Conformity	RoHS CE
------------	------------