

ZVL-E3196B

Article number: 11702382

Overview

- Evetar lens
- 7,13 mm
- F 2,4
- format 1/2,3"
- M.O.D. 0,5 m
- S-mount



Picture similar

Technical data

General data

Manufacturer Evetar

Mechanical data

Lens mount S-mount

Dimensions 19 mm × 24,97 mm

Max. length (excl. thread) 9.96 mm

Weight ≤ 6 g

Lens data

Lens resolution 5 MP

Focal length 7.13 mm

Lens data

Format 1/2.3"

Aperture F2,4

Aperture control fix

M.O.D. 0.5 m

Horizontal angle of view 47.5 °

Vertical angle of view 36.3 °

Diagonal angle of view 57.6 °

At image format 6,16 × 4,62 mm

Environmental conditions

Operating temperature -20 ... +50 °C