

ZVL-FL-CC3516-2M

Article number: 11003417

Overview

- Ricoh Imaging lens
- 35 mm
- F 1,6-16
- format 2/3"
- M.O.D. 0,35 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 35,4 mm

Max. outer diameter 29.5 mm (without knurled screws)
39.5 mm (with knurled screws)

Max. length (excl. thread) 35.4 mm

Weight ≤ 64 g

Filter thread M 27,0 × 0,5

Lens data

Lens resolution 2 MP

Lens data

Focal length 35 mm

Format 2/3"

Aperture F1,6-16

Aperture control Manual

M.O.D. 0.45 m

Horizontal angle of view 14.8 °

Vertical angle of view 11.1 °

Diagonal angle of view 18.4 °

At image format 8,8 × 6,6 mm

Environmental conditions

Operating temperature -20 ... +50 °C