

# ZVL-FL-HC0416X-VG

Article number: 11037579

## Overview

- Ricoh Imaging lens
- 4,2 mm
- F 1,6-C
- format 1/2"
- M.O.D. 0,2 m
- locating screw for aperture
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Ricoh Imaging

### Mechanical data

Lens mount C-mount

Dimensions 42 mm × 43,5 mm

Max. outer diameter 42 mm (without knurled screws)  
52 mm (with knurled screws)

Max. length (excl. thread) 43.5 mm

Weight ≤ 120 g

### Lens data

Lens resolution 0.3 MP

Focal length 4.2 mm

### Lens data

Format 1/2"

Aperture F1,6-C

Aperture control fix

M.O.D. 0.2 m

Horizontal angle of view 86.8 °

Vertical angle of view 64.3 °

Diagonal angle of view 110.2 °

At image format 6,4 × 4,8 mm

### Environmental conditions

Operating temperature -20 ... +50 °C