

ZVL-FL-HC0612A-VG

Article number: 11002840

Overview

- Ricoh Imaging lens
- 6 mm
- F 1,2-C
- format 1/2"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 46 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 46 mm

Weight ≤ 125 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 0.3 MP

Lens data

Focal length 6 mm

Format 1/2"

Aperture F1,2-C

Aperture control Manual

M.O.D. 0.2 m

Horizontal angle of view 58 °

Vertical angle of view 45 °

Diagonal angle of view 69.4 °

At image format 6,4 × 4,8 mm

Environmental conditions

Operating temperature -20 ... +50 °C