

# ZVL-M1228-MPW3

Article number: 11704871

## Overview

- Computar lens
- 12 mm
- F 2,8-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Computar

### Mechanical data

Lens mount C-mount

Dimensions 29 mm × 43.5 mm

Max. outer diameter 29 mm (without knurled screws)

Max. length (excl. thread) 44 mm

Weight ≤ 60 g

Filter thread M 27 × 0,5

### Lens data

Lens resolution 6 MP

Pixel resolution 2.74 μm

### Lens data

Focal length 12 mm

Format 2/3"

Aperture F2.8-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 40.3 °

Vertical angle of view 30.8 °

Diagonal angle of view 49.3 °

At image format 8,8 × 6,6 mm

### Environmental conditions

Operating temperature -10 ... +50 °C