



**Vue d'ensemble**

- Male straight
- M8 , 3-pole, A-coded
- 0,14 - 0,34mm<sup>2</sup>, 2,5 - 5,1mm



**Caractéristiques techniques**

Side A		Side A	
Head A: Connection	M8	Cable diameter (max.)	5,1 mm
Head A: Angle cable outlet	0°	Cable diameter (min.)	2,5 mm
Head A: Gender	Male	<b>Cables</b>	
Head A: Coding	A	Shielded	No
Head A: Shielded	No	<b>Données électriques</b>	
Head A: No. of poles	3	Operating voltage	max. 32 V AC
Head A: Width across flats	AF9	Operating current per contact	max. 4 A
Head A: Tightening torque	0,4 Nm	<b>Données mécaniques</b>	
Min. AWG	26	Head A: Degree of protection	IP67
Max. AWG	22	<b>Conditions ambiantes</b>	
Connection method	IDC terminal	Head A: Pollution degree	3
Wire cross section (max.)	0,34 mm <sup>2</sup>		
Wire cross section (min.)	0,14 mm <sup>2</sup>		