

Overview

- Female straight
- M8, 3-pole, A-coded
- 0,14 - 0,5mm², 4 - 5,5mm, shielded



Technical data

Side A

Head A: Connection	M8
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Coding	A
Head A: Shielded	Yes
Head A: No. of poles	3
Head A: Tightening torque	0.4 Nm
Min. AWG	26
Max. AWG	20
Connection method	Screw terminals
Wire cross section (max.)	0.5 mm ²

Side A

Wire cross section (min.)	0.14 mm ²
Cable diameter (max.)	5.5 mm
Cable diameter (min.)	4 mm

Electrical data

Operating current per contact	max. 4 A
-------------------------------	----------

Mechanical data

Head A: Degree of protection	IP67
------------------------------	------

Environmental conditions

Head A: Pollution degree	3
--------------------------	---