


Vue d'ensemble

- Female straight
- M8 , 4-pole, A-coded
- 0,14 - 0,34mm², 2,5 - 5,1mm



Caractéristiques techniques

Side A

Head A: Connection	M8
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Shielded	No
Head A: No. of poles	4
Head A: Width across flats	AF9
Head A: Tightening torque	0,4 Nm
Min. AWG	26
Max. AWG	22
Connection method	IDC terminal
Wire cross section (max.)	0,34 mm ²

Side A

Wire cross section (min.)	0,14 mm ²
Cable diameter (max.)	5,1 mm
Cable diameter (min.)	2,5 mm

Données électriques

Operating voltage	max. 32 V DC
Operating current per contact	max. 4 A

Données mécaniques

Head A: Degree of protection	IP67
------------------------------	------

Conditions ambiantes

Head A: Pollution degree	3
--------------------------	---