

Vue d'ensemble

- IO-Link Hub, M8 3-pin version
- 8 multifunctional DIO-Channels
- Up to 0,5 A per output
- 1 ms cycle time
- Robust fully encapsulated plastic housing (IP65, IP67)



Caractéristiques techniques

Données générales

Degree of protection	IP67
LED Indicators	Module status IO-Link Tension d'alimentation
Communication Interfaces	IO-Link
Software	Baumer Sensor Suite

Données électriques

Power supply	18 - 30 V DC
Power Consumption	40 mA

Interface de communication IO-Link

IO-Link port type	Class A
Number of input and outputs	Digital Input (DI) Digital Output (DO)
Short-circuit-proof	Oui
Reverse polarity protected	Oui

Interface de communication Digital input

Cable length	30 m
--------------	------

Interface de communication Digital output

Output current max.	0,5 A
Output function	PNP
Cable length	30 m
Short-circuit-proof	Oui
Reverse polarity protected	Oui

Données mécaniques

Model	Cubic
Width	30 mm
Height	126 mm
Depth	34,5 mm
Weight	129 g

Conditions ambiantes

Operating temperature	- 25 °C ...+ 70 °C
Storage temperature	- 40 °C ...+ 85 °C

Schéma de raccordement

