

# FUL 500D2Y00

Plastic fiber optic cable

Article number: 10159107

## Overview

- Liquid-detection type (level)
- Detection when in direct contact with media
- Cylindrical smooth sensing head  $\varnothing 4$  mm
- Plastic fiber 500 cm long, chemically resistant
- Operating temperature up to +105 °C
- For compact fiber optic sensors FVDK 10 and OF10



Picture similar

## Technical data

### General data

Particular characteristics	Chemically-resistant plastic fiber optics Liquid detection Smooth sensing head Heat-resistant plastic fiber optics
Operating principle	Liquid-detection type
Sensing distance Tw	0 mm
Measurement type	Contact with medium
Fiber optic head	Cylindrical smooth
Operating temperature	-30 ... +105 °C
Exit angle	60°
Fiber optics can be shortened to length	Yes
Integrated lens	No


### General data

Adaptable lens	No
Infrared light compatibility (1450 nm)	No

### Mechanical data

Diameter Fiber	0.5 mm
Width / diameter (head)	4 mm
Height / length (head)	15 mm
Material (head)	PFA
Bending radius (fixed)	30 mm
Cable jacket diameter	4 mm
Material cable jacket	PFA (chemically resistant)
Material (fiber optic cable)	Plastic
Length (fiber optic cable)	500 cm

## Dimension drawing



## Accessories

### Fitting fiber optic sensors

11252204	OF10.FR-GW2J.B2NV/A014
11244386	OF10.FR-GW2J.B2CV/A014
11224111	OF10.FR-PW1B.B2N
11224008	OF10.FR-NW1B.B2CV
11224009	OF10.FR-NW1B.B2N
11224110	OF10.FR-PW1B.B2CV
11244384	OF10.FR-GW2J.B2N/A014
10162867	FVDK 10N5101
10162865	FVDK 10N5101/S35A
10162866	FVDK 10P5101
10162864	FVDK 10P5101/S35A
11045446	FVDK 10N66Y0
11045448	FVDK 10N66Y0/S35A
11045460	FVDK 10N66YR
11045445	FVDK 10P66Y0
11045447	FVDK 10P66Y0/S35A
11045449	FVDK 10P66YR
11214490	FVDK 10P66ZR
11214493	FVDK 10P66Z0/S35A
11214478	FVDK 10P66Z0
11214492	FVDK 10N66ZR
11214494	FVDK 10N66Z0/S35A
11214479	FVDK 10N66Z0
11045462	FVDK 10N66YM
11045464	FVDK 10N66YS
11045461	FVDK 10P66YM
11045463	FVDK 10P66YS

### Mounting accessories

10114652	Cutting tool for plastic fiber optics
----------	---------------------------------------

### Lenses and components

10140260	Reduction tube
----------	----------------