


# Obj Kowa LM50XC 50mm/f2.0

Article number: 11166201

## Overview

- Kowa lens
- 50 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,3 m
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Kowa

### Mechanical data

Lens mount C-mount

Dimensions 44 mm × 78 mm

Max. outer diameter 44 mm (without knurled screws)  
55 mm (with knurled screws)

Max. length (excl. thread) 78 mm

Weight ≤ 220 g

Filter thread M 37,5 × 0,5

### Lens data

Pixel resolution 3 μm

### Lens data

Focal length 50 mm

Format 4/3"

Aperture F2,0-22

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 14.5 °

Vertical angle of view 10.8 °

Diagonal angle of view 18 °

At image format 12,8 × 9,6 mm

### Environmental conditions

Operating temperature -10 ... +45 °C