

# ZVL-FL-BC2518-9M

Article number: 11154325

## Overview

- Ricoh Imaging lens
- 25 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Ricoh Imaging

### Mechanical data

Lens mount C-mount  
 Dimensions 42 mm × 57,5 mm  
 Max. outer diameter 42 mm (without knurled screws)  
 52 mm (with knurled screws)  
 Max. length (excl. thread) 57.5 mm  
 Weight ≤ 149 g

### Mechanical data

Filter thread M 40,5 × 0,5

### Lens data

Lens resolution 12 MP  
 Focal length 25 mm  
 Format 1,1"  
 Aperture F1,8-16  
 Aperture control Manual  
 M.O.D. 0.1 m