

ZVL-FL-CC1214A-2M

Article number: 11150226

Overview

- Ricoh Imaging lens
- 12 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 45,7 mm

Max. outer diameter 29.5 mm (without knurled screws)
39.5 mm (with knurled screws)

Max. length (excl. thread) 45.7 mm

Weight ≤ 72 g

Lens data

Lens resolution 2 MP

Focal length 12 mm

Format 2/3"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.1 m