

ZVL-FL-HC1212B-VG

Article number: 11012527

Overview

- Ricoh Imaging lens
- 12 mm
- F 1,2-22
- format 1/2"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 30 mm × 35,5 mm
 Max. outer diameter 30 mm (without knurled screws)
 40 mm (with knurled screws)
 Max. length (excl. thread) 35.5 mm
 Weight ≤ 67 g
 Filter thread M 27,0 × 0,5

Lens data

Lens resolution 0.3 MP

Lens data

Focal length 12 mm
 Format 1/2"
 Aperture F1,2-22
 Aperture control Manual
 M.O.D. 0.2 m
 Horizontal angle of view 30.2 °
 Vertical angle of view 22.6 °
 Diagonal angle of view 37.8 °
 At image format 6,4 × 4,8 mm

Environmental conditions

Operating temperature -20 ... +50 °C