

Overview

- Ricoh Imaging lens
- 50 mm
- F 2,8-22
- format 45 mm
- M.O.D. 0,25 m
- locating screw for aperture and focus
- F-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount F-Mount
 Dimensions 72 mm × 56,8 mm
 Max. outer diameter 72 mm (without knurled screws)
 82 mm (with knurled screws)
 Max. length (excl. thread) 56.8 mm
 Weight ≤ 370 g

Mechanical data

Filter thread M 62,0 × 0,75

Lens data

Lens resolution 48 MP
 Focal length 50 mm
 Format 45 mm
 Aperture F2,8-22
 Aperture control Manual
 M.O.D. 0.25 m