

Overview

- Myutron lens
- 16 mm
- F 3.5
- format 1"
- M.O.D. 0.095 m
- locating screw for aperture and focus
- C-mount
- suitable for UV and visible wavelengths (190 - 700 nm)



Picture similar

Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount C-mount

Dimensions 51 mm × 93.8 mm

Max. outer diameter 51 mm (without knurled screws)

Max. length (excl. thread) 89.8 mm

Weight ≤ 280 g

Filter thread M49 × 0,75

Lens data

Lens resolution 8 MP

Focal length 16 mm

Focal range ≥ 12 mm ... < 25 mm

Format 1"

Aperture F3.5

Aperture control Manual

M.O.D. 0.095 m

Environmental conditions

Operating temperature 0 ... +40 °C