

ZVL-HF1635V-UV

Article number: 11728662

Overview

- Myutron lens
- 16 mm
- F 3.5
- format 1"
- M.O.D. 0.095 m
- locating screw for aperture and focus
- C-mount
- suitable for UV and visible wavelengths (190 700 nm)



Picture similar

Technical data	
General data	
Manufacturer	Myutron
Mechanical data	
Lens mount	C-mount
Dimensions	51 mm × 93.8 mm
Max. outer diameter	51 mm (without knurled screws)
Max. length (excl. thread)	89.8 mm
Weight	≤ 280 g
Filter thread	M49 × 0,75

Lens data	
Lens resolution	8 MP
Focal length	16 mm
Format	1"
Aperture	F3.5
Aperture control	Manual
M.O.D.	0.095 m
Environmental conditions	
Operating temperature	0 +40 °C