


Overview

- Myutron lens
- 35 mm
- F 3.5
- format 1"
- M.O.D. 0.191 m
- locating screw for aperture and focus
- C-mount
- suitable for UV and visible wavelengths (190 - 700 nm)



Picture similar

Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount C-mount

Dimensions 47 mm × 106 mm

Max. outer diameter 47 mm (without knurled screws)

Max. length (excl. thread) 102 mm

Weight ≤ 260 g

Filter thread M43 × 0,75

Lens data

Lens resolution 8 MP

Focal length 35 mm

Focal range ≥ 25 mm ... < 50 mm

Format 1"

Aperture F3.5

Aperture control Manual

M.O.D. 0.191 m

Environmental conditions

Operating temperature 0 ... +40 °C