

ZVL-LSF10528-U58

Article number: 11205387

Overview

- Myutron lens
- 105 mm
- F 2,8-22
- format 46 mm
- M.O.D. 0,43 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Picture similar

Technical data	
General data	
Manufacturer	Myutron
Mechanical data	
Lens mount	M58-mount
Dimensions	80 mm × 163 mm
Max. outer diameter	80 mm (without knurled screws) 90 mm (with knurled screws)
Max. length (excl. thread)	159 mm
Weight	≤ 782 g
Filter thread	M 62,0 × 0,75

Lens data	
Lens resolution	48 MP (suitable for 65 MP)
Focal length	105 mm
Format	46 mm
Aperture	F2,8-22
Aperture control	Manual
M.O.D.	0.43 m
Environmental conditions	
Operating temperature	0 +40 °C