

## ZVL-LSF20035-U58

Article number: 11205388

## Overview

- Myutron lens
- 200 mm
- F 3,5-32
- format 46 mm
- M.O.D. 0,85 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Picture similar

Technical data	
General data	
Manufacturer	Myutron
Mechanical data	
Lens mount	M58-mount
Dimensions	80 mm × 175mm
Max. outer diameter	80 mm (without knurled screws) 90 mm (with knurled screws)
Max. length (excl. thread)	252 mm
Weight	≤ 1228 q

Mechanical data	
Filter thread	$M72,0 \times 0,75$
Lens data	
Lens resolution	48 MP (suitable for 65 MP)
Focal length	200 mm
Format	46 mm
Aperture	F3,5-32
Aperture control	Manual
M.O.D.	0.85 m

Page 1 of 1