

**Overview**

- Myutron lens
- 25 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,14 m
- locating screw for aperture and focus
- F-mount



*Picture similar*

**Technical data**

**General data**

Manufacturer Myutron

**Mechanical data**

Lens mount F-Mount

Dimensions 80 mm × 107.0 mm

Max. outer diameter 80 mm (without knurled screws)  
80 mm (with knurled screws)

Max. length (excl. thread) 107 mm

Weight ≤ 750 g

Filter thread M 77,0 × 0,75

**Lens data**

Lens resolution 48 MP

Focal length 25 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.14 m

**Environmental conditions**

Operating temperature 0 ... +40 °C