

# ZVL-LSF3528-U58

Article number: 11205385

## Overview

- Myutron lens
- 35 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,23 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



*Picture similar*

## Technical data

### General data

Manufacturer Myutron

### Mechanical data

Lens mount M58-mount  
 Dimensions 62 mm × 123 mm  
 Max. outer diameter 62 mm (without knurled screws)  
 62 mm (with knurled screws)  
 Max. length (excl. thread) 118 mm  
 Weight ≤ 416 g  
 Filter thread M 52,0 × 0,75

### Lens data

Lens resolution 48 MP (suitable for 65 MP)  
 Focal length 35 mm  
 Focal range ≥ 25 mm ... < 50 mm  
 Format 44 mm  
 Aperture F2.8-22  
 Aperture control Manual  
 M.O.D. 0.23 m

### Environmental conditions

Operating temperature 0 ... +40 °C