

# ZVL-M1628-MPW3

Article number: 11704872

## Overview

- Computer lens
- 16 mm
- F 2,8-16
- format 2/3"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Computar

### Mechanical data

Lens mount C-mount

Dimensions 29 mm × 29 mm

Max. outer diameter 29 mm (without knurled screws)

Max. length (excl. thread) 29.5 mm

Weight ≤ 37 g

Filter thread M 27 × 0,5

### Lens data

Lens resolution 6 MP

Pixel resolution 2.74 μm

### Lens data

Focal length 16 mm

Format 2/3"

Aperture F2.8-16

Aperture control Manual

M.O.D. 0.25 m

Horizontal angle of view 30.7 °

Vertical angle of view 23.3 °

Diagonal angle of view 37.8 °

At image format 8,8 × 6,6 mm

### Environmental conditions

Operating temperature -10 ... +50 °C