

## Overview

- Computar lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount
- 400 - 1700 nm



*Picture similar*

## Technical data

### General data

Manufacturer Computar

### Mechanical data

Lens mount C-mount

Dimensions 33,5 mm × 36 mm

Max. outer diameter 33.5 mm

Max. length (excl. thread) 36 mm

Weight ≤ 71.2 g

Filter thread M 30,5 × 0,5

### Lens data

Lens resolution 1.3 MP

Pixel resolution 5 μm

### Lens data

Focal length 25 mm

Focal range ≥ 25 mm ... < 50 mm

Format 2/3"

Aperture F1.4-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 20.0 °

Vertical angle of view 15.1 °

Diagonal angle of view 24.9 °

At image format 8,8 mm × 6,6 mm

### Environmental conditions

Operating temperature -10 ... +50 °C