

ZVL-V1228-MPY

Article number: 11181609

Overview

- Computar lens
- 12 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 36,1 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 37.25 mm

Weight ≤ 98 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP

Lens data

Focal length 12 mm

Format 1,1"

Aperture F2,8-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 60.5 °

Vertical angle of view 46.2 °

Diagonal angle of view 71.1 °

At image format 35 × 26 mm

Environmental conditions

Operating temperature -10 ... +50 °C