


Overview

- Computar lens
- 25 mm
- F 2,0-16
- format 1"
- M.O.D. 0,15 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 37,5 mm × 44,04 mm

Max. outer diameter 37.5 mm (without knurled screws)
47.5 mm (with knurled screws)

Max. length (excl. thread) 44.6 mm

Weight ≤ 73.1 g

Filter thread M 35,5 × 0,5

Lens data

Lens resolution 20 MP

Lens data

Focal length 25 mm

Format 1"

Aperture F2,0-16

Aperture control Manual

M.O.D. 0.15 m

Horizontal angle of view 28.8 °

Vertical angle of view 21.8 °

Diagonal angle of view 35.5 °

At image format 12,8 × 9,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C