

**Overview**

- Computar lens
- 25 mm
- F 2,0-16
- format 1"
- M.O.D. 0,15 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

**Technical data**

**General data**

Manufacturer            Computar

**Mechanical data**

Lens mount              C-mount

Dimensions            37,5 mm × 44,04 mm

Max. outer diameter    37.5 mm (without knurled screws)  
47.5 mm (with knurled screws)

Max. length (excl. thread) 44.6 mm

Weight                  ≤ 73.1 g

Filter thread            M 35,5 × 0,5

**Lens data**

Lens resolution        20 MP

**Lens data**

Focal length            25 mm

Format                  1"

Aperture                F2,0-16

Aperture control        Manual

M.O.D.                  0.15 m

Horizontal angle of view 28.8 °

Vertical angle of view   21.8 °

Diagonal angle of view 35.5 °

At image format        12,8 × 9,6 mm

**Environmental conditions**

Operating temperature   -10 ... +50 °C