

Product	Shaft	Pulses per revolution, output	Connection	Material number
HOG840	Solid shaft ø11 mm	1024, HTL	1 x cable gland M20	EHO840-11730613
		2048, HTL	1 x cable gland M20	EHO840-11730659
		Parameterization at factory <sup>1)</sup>	1 x cable gland M20	EHO840-11730660
	Blind hollow shaft ø12G7	1024, HTL	1 x cable gland M20	EHO840-11730661
		2048, HTL	1 x cable gland M20	EHO840-11730662
		Parameterization at factory <sup>1)</sup>	1 x cable gland M20	EHO840-11730663
	Blind hollow shaft ø16G7	1024, HTL	1 x cable gland M20	EHO840-11730664
		2048, HTL	1 x cable gland M20	EHO840-11730665
		Parameterization at factory <sup>1)</sup>	1 x cable gland M20	EHO840-11730666

1) Please choose resolution, output stage and zero pulse (length and position) with your order

Resolution: 1...32768 ppr

Output stage: HTL-P or TTL

Zero pulse:

- 90°, K1=K2=1

- 180°, K1=0

- 180°, K2=0

- 180°, K1=1

Example for EHO840 - 11730660: 5000 ppr, TTL, 180°, K2=0