

# VCXG.2-201M.R

Gigabit Ethernet, 20 Megapixel, Monochrome

Article number: 11708153

## Overview

- 5472 x 3648 px
- Sony IMX183
- 1" CMOS
- 6 fps
- Gigabit Ethernet



Picture similar



GEN*i*CAM



## Technical data

### Sensor information

Sensor	Sony IMX183
Mono/Color	Mono
Sensor type	1" CMOS
Shutter type	Rolling shutter Global reset shutter
Resolution	5472 × 3648 px
Pixel size	2.4 × 2.4 μm
Exposure time	0.115 ... 60000 ms

### Data quality (EMVA 1288 typical)

Dark noise	3.11 e-
Saturation capacity	14844 e-
Dynamic range	71.7 dB
Signal-to-noise ratio	41.7 dB
Quantum efficiency	78.2 % @ 535 nm

### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5472 × 3648 px, max. 6 fps Binning 2×2, 2736 × 1824 px, max. 9 fps Binning 2×1, 2736 × 3648 px, max. 9 fps Binning 1×2, 5472 × 1824 px, max. 9 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5472 × 3648 px, max. 9 fps
Pixel formats	Mono8 Mono10 Mono12 Mono12 Packed

### Image preprocessing

Analog controls	Gain (0 ... 20 dB) Offset (0 ... 255 LSB 12 Bit)
Color models	Mono
<b>Camera features</b>	
Basic Functions	Exposure Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
Auto Functions	Exposure Auto Gain Auto
Image Pre-processing	LUT / Gamma
Acquisition / Interface	Burst Mode Adjustable Framerate Device Link Throughput Limit Internal Image Buffer
Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals

# VCXG.2-201M.R

Gigabit Ethernet, 20 Megapixel, Monochrome

Article number: 11708153

## Technical data

### Camera features

Process Synchronization	Events Timer Trigger Delay Debouncer Counter Trigger via Action CMD (GigE) Additional Output Modes (e.g. Trigger Ready) Chunk data inside transferred image Encoder support via Counter End trigger source
-------------------------	--

Additional Functions	User Set Integrated temperature sensor Readable additional information (e.g. sensor information)
----------------------	--

Calibration data	Camera calibration data (user defined storage for intrinsic / extrinsic camera parameters, and geometry distortion values) Customer data storage (128 bytes user defined)
------------------	--

Internal image buffer	58 MB 1 image (Trigger Mode) 1 image (Free Running Mode)
-----------------------	--

### Interfaces and connectors

Data interface	Gigabit Ethernet, Transfer rate 1000 Mbits/sec, Fast Ethernet, Transfer Rate 100 Mbits/sec, Connector: 8P8C Modular Jack (RJ45), screwable type
----------------	---

Process interface	M8 / 8 pins (SACC-DSI-M8MS-8CON-M8-L180)
-------------------	--

Power supply	via M8/8 pins or Power over Ethernet (PoE)
--------------	--

### Mechanical data

Lens mount	C-mount
------------	---------

Width	29 mm
-------	-------

Height	29 mm
--------	-------

Depth	49 mm
-------	-------

Weight	≤ 120 g
--------	---------

Material	zinc die casting, baked varnish
----------	---------------------------------

### Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
--------------------------	--

Power consumption	Approx. 2.8 W @ 12 VDC and 6 fps Approx. 3.4 W @ 48 VDC (PoE) and 6 fps
-------------------	--

### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

### Environmental conditions

Operating temperature	0 ... +65 ° @ T = measurement point
-----------------------	-------------------------------------

Storage temperature	-20 ... +70 °C
---------------------	----------------

Humidity	10 ... 90 % (non-condensing)
----------	------------------------------

Protection class	IP 40 (with mounted lens and cable)
------------------	-------------------------------------

### Digital I/Os

Lines	1 input line 1 output line 2 general purpose lines
-------	--

### Conformity

Conformity	CE RoHS
------------	------------

## Dimension drawing

