

Overview

- PROFINET and EtherNet/IP interface integrated
- FEX image processor
- User management
- Password protection
- Backup & Restore function
- Download VeriSens Application Suite: www.baumer.com/vs-sw



Picture similar



Technical data

General data		Electrical data	
Resolution	752 × 480 px	Digital inputs	5 inputs trigger job selection external teach-in encoders (CH-A, CH-B) 500 kHz
Sensor type	1/3" CMOS, monochrome	Outputs	PNP $I_{peak} = 100\text{ mA}$ and $I_{eff} = 50\text{ mA}$ (short-circuit proof)
Illumination	integrated, LED white	Digital outputs	5 outputs Pass / Fail Flash Sync Alarm Camera Ready Output Enable
LED class	risk group 1 (low risk, EN 62471:2008)	Initial setup	Ethernet (10BASE-T / 100BASE-TX)
High-resolution mode	max. 50 inspections per second	Process interface	PROFINET (CC-A) EtherNet/IP™ TCP/UDP (Ethernet)
Object distance min.	50 mm	Visualization	configurable web interface with <i>Mul-tiViewer</i> function
Object distance max.	450 mm	Mechanical data	
Number of jobs (products)	≤ 255	Width	53 mm
Features per job	32	Height	99.5 mm
Signal processing	Baumer FEX® 4.0	Depth	38 mm
Defect image memory	32	Weight	≤ 250 g
Lens	12 mm	Material	housing: aluminum cover glass: PMMA
Electrical data			
Nominal voltage power supply	24 V +- 25%		
Nominal voltage power supply (add-on)	Class 2 according to NEC / protection class III		
Nominal voltage power supply (info)	The device is intended for supply from an isolated limited power source according to UL61010-1, 3rd ed cl. 9.4 or a limited energy source according to UL60950-1 or Class 2 according to NEC.		
Power consumption	Max. 18 W (with I/O)		
Inputs	8 ... 30 V (polarity protected)		

2023-07-18 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Technical data

Environmental conditions

Operating temperature	+5 ... +60 °C @ T = measurement point
Storage temperature	-20 ... +70 °C
Humidity	0 ... 90 % (non-condensing)
Protection class	IP 67
Vibration load	IEC 60068-2-6 IEC 60068-2-64
Mechanical shock resistance	EN 60068-2-27

Code types

Barcode	2/5 Industrial 2/5 Interleaved Codabar Code 39 Code 93 Code 128 PharmaCode EAN 8 EAN 13 UPC-A UPC-E GS1 DataBar GS1 128
---------	---

Code types

Matrix code	DataMatrix (ECC 200) GS1-DataMatrix QR-Code PDF417
Font	many font styles (recommended: sans serif, proportional) Dot Matrix characters: A-Z a-z 0-9 + - . : / ()

Feature checks

Part location	part location on text line
Feature comparison	contour comparison
Identification	Barcode Matrix code text

Conformity

Conformity	CE RoHS KC (R-REI-BkRR-VeriSens-IP) UL
------------	---

Non-volatile memory

Flash memory size	256 Mbit Flash S29GL256P10FFI010
-------------------	----------------------------------

Electrical connection



1: PWR (+18-30 V DC)	7: OUT3
2: Ground	8: IN3
3: IN1 (Trigger)	9: OUT4
4: OUT1	10: IN4
5: IN2	11: IN5
6: OUT2	12: OUT5



1: TD+	3: TD-
2: RD+	4: RD-

Dimension drawing

