


Vue d'ensemble

- M12, female, A-coded, 12-poles; PVC, 150 cm; M12, male, A-coded, 5-poles
- Head A: IP65, IP66K, IP67; Head B: IP67
- Cable: Good resistance against chemicals


Caractéristiques techniques
Side A

Head A: Connection	M12
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Coding	A
Head A: No. of poles	12
Head A: LED	No
Head A: Width across flats	AF13
Head A: Tightening torque	0,6 Nm
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni
Head A: Body color	Black
Head A: Gasket material	FKM
Labeling sleeve side A	Yes

Side B

Head B: Connection	M12
Head B: Angle cable outlet	0°
Head B: Gender	Male
Head B: Coding	A
Head B: No. of poles	5
Head B: LED	No
Head B: Knurled nut material	Brass, surface Ni
Head B: Body color	Black
Head B: Gasket material	TPE-A – Pebax 4033
Labeling sleeve side B	Yes

Cables

Cable length	150 cm
Length tolerance	+ 10 cm
Shielded	No
Conductor structure	18 × 0,1 mm
AWG	26
External sheath: Material	PVC
External sheath: Color	Black
Cable diameter	6 mm ± 5%
Wire cross section	0,14 mm ²

Cable

External sheath: Shore hardness	75 ± 5 A
Cable: Temperature range (mobile)	- 5 ...+ 70 °C
Cable: Temperature range (fixed)	- 30 ...+ 70 °C
Shielded	No
Bending radius (fixed)	60 mm
Number of wires	12

Cable

Number and diameter of wires	12x0,14
Length tolerance	+ 10 cm
Cable length	150 cm
AWG	26
Bending radius (mobile)	min. 10 × outer diameter
Cable weight	approx. 55 g/m
Conductor structure	18 × 0,1 mm
Cable diameter	6 mm ± 5%
Conductor: Material	Copper, bare
External sheath: Material	PVC
Insulation: Material	PVC
Nominal voltage	300 V
Paired stranding	No
Single wire diameter	0,1 mm
Cable: Test voltage	1,5 kV 0
Wire cross section	0,14 mm ²
Wire processing	No
Wire diameter incl. isolation	1 mm ± 5%
External sheath: Color	Black

Données électriques

Operating voltage	max. 30 V AC/DC 0
Nominal voltage	300 V
Contact resistance	max. 30 mOhm
Operating current per contact	max. 1,5 A

Données mécaniques

Head A: Degree of protection	IP65, IP66K, IP67
Head B: Degree of protection	IP67
Bending radius (mobile)	min. 10 × outer diameter

Conditions ambiantes

Temperature range (mobile)	- 5 ...+ 70 °C
Temperature range (fixed)	- 25 ...+ 70 °C
Cable: Temperature range (fixed)	- 30 ...+ 70 °C
Dragchain capable	No
Head A: Chemical resistance	No
Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	ASTM 1 oil, mineral oils, limited to hydraulic oils
Head A: Acid and alkali resistant	No

Caractéristiques techniques

Conditions ambiantes


Head A: Pollution degree	3
Head B: Pollution degree	3
Cable: Chemical resistance	Good

Conditions ambiantes

Cable: Oil resistance	Good
Cable: Silicone-free	Oui


Side A

Technical drawing



Side B

Coding



Coding





Schéma de raccordement



Dessin d'encombrement

