


Vue d'ensemble

- M12, male, A-coded, 5-poles; PUR, 2000 cm; M12, female, 90°, A-coded, 5-poles
- Dragchain capable, suitable for robotics ± 180 °/m
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames and oils
- Halogen free



Caractéristiques techniques

Side A		Cables	
Head A: Connection	M12	Wire cross section	0,34 mm ²
Head A: Angle cable outlet	0°	Cable	
Head A: Gender	Male	Shielded	No
Head A: Coding	A	Cable length	2000 cm
Head A: No. of poles	5	AWG	22
Head A: LED	No	Torsion speed	max. 35 cycles/min
Head A: Width across flats	AF14	Conductor: Material	Copper, bare
Head A: Tightening torque	0,6 Nm	External sheath: Material	TPE-S
Head A: Knurled nut material	Stainless steel (V4A)	Insulation: Material	PP
Head A: Body color	Blue	Paired stranding	No
Labeling sleeve side A	No	Torsion stress in °	± 180 °/m
Side B		Total stranding	5 wires strand around core-filler
Head B: Connection	M12	Wire cross section	0,34 mm ²
Head B: Angle cable outlet	90°	Wire processing	No
Head B: Gender	Female	External sheath: Color	Blue
Head B: Coding	A	Données mécaniques	
Head B: No. of poles	5	Head A: Degree of protection	IP65, IP68, IP69K
Head B: LED	No	Head B: Degree of protection	IP65, IP68, IP69K
Head B: Width across flats	AF14	Torsion speed	max. 35 cycles/min
Head B: Knurled nut material	Stainless steel (V4A)	Torsion stress in °	± 180 °/m
Head B: Body color	Blue	Conditions ambiantes	
Head B: Gasket material	EPDM	Dragchain capable	Oui
Labeling sleeve side B	No	Head A: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Cables		Head A: Flame resistance	HB (UL 94)
Cable length	2000 cm		
Shielded	No		
AWG	22		
External sheath: Material	TPE-S		
External sheath: Color	Blue		

Caractéristiques techniques
Conditions ambiantes

Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.
Head A: Acid and alkali resistant	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head A: Pollution degree	3
Head B: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head B: Flame resistance	HB (UL 94)
Head B: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

Conditions ambiantes

Head B: Acid and alkali resistant	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head B: Pollution degree	3
Cable: Acid and alkali resistant	Good (analogue FDA 21 178.3620, 178.3297, 177.1520)
Cable: Silicone-free	Oui

Commercial data

Eclass	27060311
--------	----------