


Axle speed measurement.

BPIV2 — Multi-channel axle encoder with field-exchangeable bearing package.

Baumer's innovative axle encoder portfolio provides reliable and proven solutions for speed measurement with additional measurement functionalities for acceleration, temperature and torsional vibration. The robust magnetic sensing technology offers superb signal quality and flexibility.


- Drastically simplified axle configuration for minimized cabling and faster installation
- Multi-unit design with up to four independent encoder units per axle encoder
- Each encoder unit is individually configurable to meet the specific requirements of any subsystem
- Incremental outputs for current and voltage can be freely combined in an axle encoder
- Freely configurable number of pulses up to 1200 ppr, separately for each encoder unit
- Smart functions, such as direction of rotation, digital speed threshold, heartbeat signal
- Fully integrated axle encoder allows easy mounting without any adjustments
- Optimal solution for vehicles with few available axle ends, e.g. locos
- Simple retrofitting without additional effort due to standard mechanical interfaces
- Optimum and custom-fit solutions due to the wide range of configuration options such as freely selectable number of pulses per encoder unit, various coupling types, cables and connectors





Main application fields

- Traction control
- Torsional vibration detection
- Wheel slide protection
- Train control
- Juridical recording
- Speed indication
- Hot box detection
- Bogie hunting and derailment detection



Torsional vibration detection

Reliable, accurate and fast torsional vibration detection is key to increase traction performance, wheel set lifetime and safety. BPIV2 signals enable torsional vibration detection with ultimate dynamics and precision, by unsurpassed signal quality and robustness, high resolution and minimal backlash. This cuts down on wear while improving traction and passenger comfort.

Product overview BPIV2





| | BPIV2 |
|--|---|
| Pulses per revolution | Max. 1200 ppr (configurable for each encoder unit) |
| Number of incremental signals per encoder unit | 2 (A 90° B) |
| Number of encoder units per axle encoder | Max. 4 |
| Phase shift between incremental signals of an encoder unit | 90° |
| Duty cycle of incremental signals | 50 % |
| Voltage supply | 10.8 26.4 VDC (class S1 according EN 50155) |
| Current consumption per encoder unit | Typ. 40 mA at 15 VDC (push-pull, without load) Typ. 50 mA at 21 VDC (current) |
| Sensor output circuits - push-pull | Load max. ±30 mA UHIGH min. = +Vs - 2.5 V, ULOW max. = 2.5 V |
| Sensor output circuits - current | LOW: min. 5 mA, HIGH: max.16 mA, Δ LOW-HIGH: 7 8 mA TRISTATE: max. 0.1 mA, Load resistance: 230 Ω ±10 % (others on request) |
| Cutoff frequency | 40 kHz |
| Reverse polarity and short circuit protection | Yes |
| Insulation resistance | Min. 100 MΩ at 500 VDC |
| Dielectric strength | 1500 VAC (EN 50155) |
| Ambient temperature | Class OT4 (EN 50155), -40 +70 °C |
| Protection | Bearing side IP 65, rest IP 69 |
| Shock and vibration | Category 3 (EN 61373) |
| Fire hazard level | HL3 (EN 45545-2) |
| Identification | GS1 compliant product labels with GIAI and GTIN |
| Safety integrity level | SIL2 (EN 50128, EN 50129) |
| Cable conduit type | Synthetic rubber tube, ø24.9 mm |
| Coupling | Various coupling variants on request |

Additional options available on request: Temperature sensor, acceleration sensor, function control signal, digital speed threshold signal, direction of rotation signal and communication interfaces.

Additional information on our railway solutions: www.baumer.com/railway

Find your local Partner: www.baumer.com/worldwide



Baumer Group
International Sales
P.O. Box
Hummelstrasse 17
CH-8501 Frauenfeld
Phone +41 52 728 1122
Fax +41 52 728 1144
sales.ch@baumer.com