

Overview

- Computar lens
- 12 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 36,1 mm
 Max. outer diameter 42 mm (without knurled screws)
 52 mm (with knurled screws)
 Max. length (excl. thread) 37.25 mm
 Weight ≤ 98 g
 Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP

Lens data

Focal length 12 mm
 Format 1,1"
 Aperture F2,8-16
 Aperture control Manual
 M.O.D. 0.3 m
 Horizontal angle of view 60.5 °
 Vertical angle of view 46.2 °
 Diagonal angle of view 71.1 °
 At image format 35 × 26 mm

Environmental conditions

Operating temperature -10 ... +50 °C