

# Baumer ZVI-BL-310/54-R

Article number: 11731511

### Overview

- Flashable red LED bar light
- Red (625 nm)Radiation angle 100°
- Integrated LED controller with 4 operating modes



Picture similar







Technical data			
General data			
Manufacturer	Baumer		
Illumination data			
Color / Peak wavelength	red (625 nm)		
Beam angle	100°		
Operating modes	steady light steady light with brightness control flashed light with PNP sourcing flashed light with NPN sourcing		
Recommended illumination distance	10 mm 500 mm		
Electrical data			
Connectors	M8/4-pin male connector		
Operating voltage	24 VDC		
Maximum flash duration	20 ms		
Power consumption	approx. 18 W (steady light) approx. 56 W (flashed light)		

Mechanical data	
Construction design	bar light
Dimensions	54 mm x 310 mm x 23 mm
Dimensions luminous area	45 mm x 300 mm
Material of cover glass	PMMA (acrylic glass)
Material of housing	aluminum (anodized, black)
Weight	≤ 560 g
Environmental conditions	
Operating temperature	0 +30 °C 0 +45 °C with thermal connection
Conformity	CE RoHS
Humidity	30 70 %
Protection class	IP 54

# Baumer ZVI-BL-310/54-R

Article number: 11731511





PW=f(Udim) t DIM (Pin2) is used as brightness control and

operation mode switch. It's a high resistance current sink with 0.2 mA for 5 V and 1 mA for 24 V.

PWM frequency: 3.8 kHz Min. exposure time: 5 ms

Flas	h light			
I <sub>LED</sub> 4			\	
		Trigger signal		
		20 ms		t

Triggered flash light with overdrive current and time-out for LED protection. Max. flash time:


Min. flash time: 100µs Latency (trigger -> LED ON): max 30µs Max. clock speed: 1 kHz

Max. duty cycle:


25 %

## Pin assignment M8 socket, 4-pin

#### Pin Core color Description 1 brown 24 VDC 2 white Dim 3 blue Trigger 4 black Ground




### **Connection examples**







# Baumer ZVI-BL-310/54-R


Article number: 11731511




steady light with brightness control









#### Safety notes









Read the warning and application instructions carefully and completely before working with this device.

Only operate the illumination in compliance with the prescribed protective measures. It is essential to ensure compliance with the permissible ambient conditions.

The device is only designed for indoor use.

#### Light:

Due to the risk of eye irritation or injury, it is not recommended to look directly into the light source. The illumination system must be switched off before installation and/or maintenance. The device must not be used if incorrect operation may cause personal injury.

#### Heat:

The surface temperature may exceed 60 °C if heat dissipation is inadequate or when the illumination is operated in flash mode with an excessively high duty cycle. Keep away from flammable materials by all means.

### **Electricity:**

The housing is electrically isolated from the power supply ground. Exceeding the permissible input voltage Uin or ULED(+) may cause damage to the device or significantly shorten the service life of the LEDs within the device.

#### Usage:

Do not apply mechanical stress to the luminous area during operation. This will result in inhomogeneous light emission.

#### Cleaning:

The light surface must be cleaned with a conventional glass cleaner and a soft cleaning cloth. Avoid using other cleaning agents as these can damage the device.

#### Installation:

To maximize the service life of the LED, it is important to avoid heat build-up. To do so, install the lighting with a proper thermal connection. Be sure to hand-tighten the cables, do not overtighten.