


Overview

- M12, female, A-coded, 5-poles; PVC, 200 cm, open cable end
- Head A: IP65, IP66K, IP67



Technical data

Side A		Cable	
Head A: Connection	M12	Number of wires	5
Head A: Angle cable outlet	0°	Number and diameter of wires	5x0.34
Head A: Gender	Female	Cable length	200 cm
Head A: Coding	A	AWG	22
Head A: No. of poles	5	Bending radius (fixed)	min. 5 × outer diameter
Head A: LED	No	Bending radius (mobile)	min. 10 × outer diameter
Head A: Width across flats	AF13	Cable type	1
Head A: Tightening torque	0.6 Nm	Conductor structure	19 × 0.15 mm
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni	Cable diameter	5.2 mm ± 5%
Head A: Body color	Black	Conductor: Material	Copper, bare
Head A: Gasket material	FKM	External sheath: Material	PVC
Labeling sleeve side A	Yes	Insulation: Material	PVC
Side B		Nominal voltage	300 V AC
Head B: Connection	Open-ended wires	Paired stranding	No
Labeling sleeve side B	Yes	Single wire diameter	0.15 mm
Cables		Cable: Test voltage	2 kV
Cable length	200 cm	Total stranding	5 wires strand around core-filler
Shielded	No	Wire cross section	0.34 mm ²
Conductor structure	19 × 0.15 mm	Wire processing	No
AWG	22	Wire diameter incl. isolation	1.25 mm ± 5%
External sheath: Material	PVC	External sheath: Color	Gray
External sheath: Color	Gray	Electrical data	
Cable diameter	5.2 mm ± 5%	Operating voltage	max. 125 V AC/DC 0
Wire cross section	0.34 mm ²	Nominal voltage	300 V AC
Cable		Contact resistance	max. 30 mOhm
Cable: Temperature range (mobile)	- 5 ...+ 80 °C	Operating current per contact	max. 4 A
Cable: Temperature range (fixed)	- 30 ...+ 80 °C	Mechanical data	
Shielded	No	Head A: Degree of protection	IP65, IP66K, IP67

Technical data
Mechanical data

Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter

Environmental conditions

Temperature range (mobile)	- 5 ...+ 80 °C
Temperature range (fixed)	- 25 ...+ 80 °C
Cable: Temperature range (fixed)	- 30 ...+ 80 °C
Dragchain capable	No
Head A: Chemical resistance	No
Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

Environmental conditions

Head A: Acid and alkali resistant	No
Head A: Pollution degree	3
Cable: Chemical resistance	Good
Cable: Flame resistance	Conform UL 1581 VW-1
Cable: Oil resistance	Good
Cable: Silicone-free	Yes

Commercial data

Eclass	27060311
--------	----------