


Vue d'ensemble

- M12, female, A-coded; 5-poles; TPE-S, 1500 cm, free cable end
- Dragchain capable; suitable for robotics $\pm 180^\circ/\text{m}$; suitable for food & beverage
- Head A: IP65, IP68, IP69K
- ECOLAB tested
- Halogen free



Caractéristiques techniques

Side A		Cable	
Head A: Connection	M12	Length tolerance	$\pm 22,5$ cm
Head A: Angle cable outlet	90°	Cable length	1500 cm
Head A: Gender	Female	Acceleration (C-track)	max. 10 m/s ²
Head A: Coding	A	AWG	22
Head A: No. of poles	5	Bending radius (fixed)	min. 5 × outer diameter
Head A: LED	No	Torsion speed	max. 35 cycles/min
Head A: Width across flats	AF14	Bending radius (mobile)	min. 10 × outer diameter
Head A: Tightening torque	0,6 Nm	Cable weight	approx. 35,2 g/m
Head A: Knurled nut material	Stainless steel (V4A)	Conductor structure	42 × 0,1 mm
Head A: Body color	Blue	Cable diameter	5 mm $\pm 5\%$
Head A: Gasket material	EPDM	Conductor: Material	Copper, bare
Labeling sleeve side A	No	External sheath: Material	TPE-S
		Insulation: Material	PP
Side B		No. of bending cycles (C-track)	approx. 400000 Cycles
Head B: Connection	Open-ended wires	Nominal voltage	300 V AC
Labeling sleeve side B	No	No. of torsion cycles	approx. 2000000 Cycles
Cables		Paired stranding	No
Cable length	1500 cm	Single wire diameter	0,1 mm
Length tolerance	$\pm 22,5$ cm	Cable: Test voltage	3 kV
Stripping length	20 mm	Torsion stress in °	$\pm 180^\circ/\text{m}$
Shielded	No	Total stranding	5 wires strand around core-filler
Conductor structure	42 × 0,1 mm	Travel speed (C-track)	max. 3 m/s
AWG	22	Traversing path (horizontal)	max. 10 mm
External sheath: Material	TPE-S	Wire cross section	0,34 mm ²
External sheath: Color	Blue	Wire processing	No
Cable diameter	5 mm $\pm 5\%$	Wire diameter incl. isolation	1,27 mm $\pm 5\%$
Wire cross section	0,34 mm ²	External sheath: Color	Blue
Cable		Données électriques	
Cable: Temperature range (mobile)	- 25 ...+ 105 °C	Operating voltage	max. 125 V AC/DC
Cable: Temperature range (fixed)	- 40 ...+ 105 °C	Operating voltage (only UL listed)	30 V AC/DC
Operating voltage (only UL listed)	30 V AC/DC	Nominal voltage	300 V AC
Shielded	No	Contact resistance	max. 30 mOhm
Bending radius (fixed)	25 mm	Operating current per contact	max. 4 A
Number of wires	5	Données mécaniques	
Number and diameter of wires	5x0,34	Head A: Degree of protection	IP65, IP68, IP69K

Caractéristiques techniques

Données mécaniques

Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 5 × outer diameter
No. of bending cycles (C-track)	approx. 4000000 Cycles
Torsion speed	max. 35 cycles/min
Torsion stress in °	± 180 °/m
No. of torsion cycles	approx. 2000000 Cycles
Acceleration (C-track)	max. 10 m/s ²
Travel speed (C-track)	max. 3 m/s

Conditions ambiantes

Temperature range (mobile)	- 25 ...+ 105 °C
Temperature range (fixed)	- 40 ...+ 105 °C
Cable: Temperature range (fixed)	- 40 ...+ 105 °C
Dragchain capable	Oui

Conditions ambiantes

Head A: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	ASTM 1 oil, mineral oils, limited to hydraulic oils
Head A: Acid and alkali resistant	ECOLAB tested
Head A: Pollution degree	3
Cable: Chemical resistance	ECOLAB material resistance test passed
Cable: Acid and alkali resistant	Good (FDA 21 178.3620, 178.3297, 177.1520, EU 10/2011)
Cable: Silicone-free	Oui

Commercial data

Eclass	27060311
--------	----------


Side A

Technical drawing



Side B

Technical drawing



Coding




Schéma de raccordement

1	BN
2	WH
3	BU
4	BK
5	GY

Dessin d'encombrement

