

Vue d'ensemble

- M12, male, D-coded; 4-poles; TPE-S, 500 cm, shielded, free cable end
- Dragchain capable; suitable for robotics $\pm 180^\circ/\text{m}$; suitable for food & beverage
- Head A: IP65, IP68, IP69K
- Halogen free


Caractéristiques techniques

Side A		Cable	
Head A: Connection	M12	Acceleration (C-track)	max. 2 m/s ²
Head A: Angle cable outlet	0°	AWG	22
Head A: Gender	Male	Bending radius (fixed)	min. 5 × outer diameter
Head A: Coding	D	Torsion speed	max. 35 cycles/min
Head A: No. of poles	4	Bending radius (mobile)	min. 15 × outer diameter
Head A: LED	No	Cable weight	approx. 61,6 g/m
Head A: Width across flats	AF14	Conductor structure	7 × 0,25 mm
Head A: Tightening torque	0,6 Nm	Cable diameter	6,5 mm ± 5%
Head A: Knurled nut material	Stainless steel (V4A)	Conductor: Material	Copper, bare
Head A: Body color	Blue	External sheath: Material	TPE-S
Labeling sleeve side A	No	Insulation: Material	PP
Side B		Shielding: Material	Copper, tinned
Head B: Connection	Open-ended wires	No. of bending cycles (C-track)	approx. 2000000 Cycles
Labeling sleeve side B	No	Nominal voltage	300 V AC
Cables		No. of torsion cycles	approx. 2000000 Cycles
Cable length	500 cm	Paired stranding	No
Length tolerance	± 7,5 cm	Single wire diameter	0,25 mm
Stripping length	20 mm	Cable: Test voltage	3 kV AC
Shielded	Oui	Torsion stress in °	± 180 °/m
Conductor structure	7 × 0,25 mm	Total stranding	4 wires strand around core-filler
AWG	22	Travel speed (C-track)	max. 3,3 m/s
External sheath: Material	TPE-S	Traversing path (horizontal)	max. 5 m
External sheath: Color	Blue	Wire cross section	0,34 mm ²
Cable diameter	6,5 mm ± 5%	Wire processing	No
Wire cross section	0,34 mm ²	Wire diameter incl. isolation	1,55 mm ± 5%
Cable		External sheath: Color	Blue
Cable: Temperature range (mobile)	- 20 ... + 80 °C	Protocols	CAT5e
Cable: Temperature range (fixed)	- 40 ... + 80 °C	Données électriques	
Shielded	Oui	Operating voltage	max. 60 V DC
Shielding: Covering	approx. 85 %	Nominal voltage	300 V AC
Bending radius (fixed)	32,5 mm	Contact resistance	max. 30 mOhm
Number of wires	4	Operating current per contact	max. 4 A
Number and diameter of wires	4x0,34	Données mécaniques	
Length tolerance	± 7,5 cm	Head A: Degree of protection	IP65, IP68, IP69K
Cable length	500 cm	Bending radius (mobile)	min. 15 × outer diameter
		Bending radius (fixed)	min. 5 × outer diameter

Caractéristiques techniques

Données mécaniques

No. of bending cycles (C-track)	approx. 2000000 Cycles
Torsion speed	max. 35 cycles/min
Torsion stress in °	± 180 °/m
No. of torsion cycles	approx. 2000000 Cycles
Acceleration (C-track)	max. 2 m/s ²
Travel speed (C-track)	max. 3,3 m/s

Conditions ambiantes

Temperature range (mobile)	- 20 ...+ 80 °C
Temperature range (fixed)	- 40 ...+ 80 °C
Cable: Temperature range (fixed)	- 40 ...+ 80 °C
Dragchain capable	Oui
Head A: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.

Conditions ambiantes


Head A: Flame resistance	HB (UL 94)
Head A: Oil resistance	ASTM 1 oil, mineral oils, limited to hydraulic oils
Head A: Acid and alkali resistant	ECOLAB tested
Head A: Pollution degree	3
Cable: Acid and alkali resistant	Good (FDA 21 178.3620, 178.3297, 177.1520, EU 10/2011)
Cable: Silicone-free	Oui

Commercial data

Eclass	27061801
--------	----------

Side A

Technical drawing



Side B

Technical drawing





Schéma de raccordement



Dessin d'encombrement

