


Vue d'ensemble

- M12, female, A-coded, 5-poles; PVC, 500 cm, open cable end
- Head A: IP65, IP66K, IP67



Caractéristiques techniques

Side A		Cable	
Head A: Connection	M12	Number of wires	5
Head A: Angle cable outlet	0°	Number and diameter of wires	5x0,34
Head A: Gender	Female	Cable length	500 cm
Head A: Coding	A	AWG	22
Head A: No. of poles	4	Bending radius (fixed)	min. 5 × outer diameter
Head A: LED	No	Bending radius (mobile)	min. 10 × outer diameter
Head A: Width across flats	AF14	Cable type	1
Head A: Tightening torque	0,6 Nm	Conductor structure	19 × 0,15 mm
Head A: Knurled nut material	Stainless steel (V4A)	Cable diameter	5,2 mm ± 5%
Head A: Body color	Gray	Conductor: Material	Copper, bare
Head A: Gasket material	FKM	External sheath: Material	PVC
Labeling sleeve side A	No	Insulation: Material	PVC
Side B		Nominal voltage	300 V AC
Head B: Connection	Open-ended wires	Paired stranding	No
Labeling sleeve side B	No	Single wire diameter	0,15 mm
Cables		Cable: Test voltage	2 kV
Cable length	500 cm	Total stranding	5 wires strand around core-filler
Shielded	No	Wire cross section	0,34 mm ²
Conductor structure	19 × 0,15 mm	Wire processing	No
AWG	22	Wire diameter incl. isolation	1,25 mm ± 5%
External sheath: Material	PVC	External sheath: Color	Gray
External sheath: Color	Gray	Données électriques	
Cable diameter	5,2 mm ± 5%	Operating voltage	max. 125 V AC/DC 0
Wire cross section	0,34 mm ²	Nominal voltage	300 V AC
Cable		Contact resistance	max. 30 mOhm
Cable: Temperature range (mobile)	- 5 ...+ 80 °C	Operating current per contact	max. 4 A
Cable: Temperature range (fixed)	- 30 ...+ 80 °C	Données mécaniques	
Shielded	No	Head A: Degree of protection	IP65, IP68

Caractéristiques techniques
Données mécaniques

Bending radius (mobile) min. 10 × outer diameter

Bending radius (fixed) min. 5 × outer diameter

Conditions ambiantes

Temperature range (mobile) - 5 ...+ 80 °C

Temperature range (fixed) - 25 ...+ 80 °C

Cable: Temperature range (fixed) - 30 ...+ 80 °C

Dragchain capable No

Head A: Chemical resistance No

Head A: Flame resistance HB (UL 94)

Head A: Oil resistance Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

Conditions ambiantes

Head A: Acid and alkali resistant No

Head A: Pollution degree 3

Cable: Chemical resistance Good

Cable: Flame resistance Conform UL 1581 VW-1

Cable: Oil resistance Good

Cable: Silicone-free Oui

Commercial data

Eclass 27060311