

Overview

- M8, male, A-coded, 4-poles; PUR, 2500 cm; M8, female, A-coded, 4-poles
- Dragchain capable; suitable for robotics $\pm 180^\circ/\text{m}$
- Head A: IP65, IP66K, IP67; Head B: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames, oils
- Halogen free



Technical data

| Side A | | Cable | |
|---------------------------------|---------------------------------------|------------------------------------|--------------------------|
| Head A: Connection | M8 | Cable: Temperature range (mobile) | - 25 ...+ 80 °C |
| Head A: Angle cable outlet | 0° | Cable: Temperature range (fixed) | - 40 ...+ 80 °C |
| Head A: Gender | Male | Operating voltage (only UL listed) | 30 V AC/DC |
| Head A: Coding | A | Shielded | No |
| Head A: No. of poles | 4 | Bending radius (fixed) | 22.5 mm |
| Head A: LED | No | Number of wires | 4 |
| Head A: Width across flats | AF9 | Number and diameter of wires | 4x0.25 |
| Head A: Tightening torque | 0.4 Nm | Length tolerance | ± 37.5 cm |
| Head A: Knurled nut material | Brass, surface Ni | Cable length | 2500 cm |
| Head A: Body color | Black | Acceleration (C-track) | max. 10 m/s ² |
| Labeling sleeve side A | Yes | AWG | 24 |
| Side B | | Bending radius (fixed) | min. 5 × outer diameter |
| Head B: Connection | M8 | Torsion speed | max. 35 cycles/min |
| Head B: Angle cable outlet | 0° | Bending radius (mobile) | min. 10 × outer diameter |
| Head B: Gender | Female | Cable type | 3 |
| Head B: Coding | A | Cable weight | approx. 33 g/m |
| Head B: No. of poles | 4 | Conductor structure | 32 × 0.1 mm |
| Head B: LED | No | Cable diameter | 4.5 mm \pm 5% |
| Head B: Width across flats | AF9 | Conductor: Material | Copper, bare |
| Head B: Tightening torque | 0.4 Nm | External sheath: Material | PUR |
| Head B: Knurled nut material | Zinc-pressure die casting, surface Ni | Insulation: Material | PP |
| Head B: Body color | Black | No. of bending cycles (C-track) | approx. 10000000 Cycles |
| Head B: Gasket material | FKM | Nominal voltage | 300 V |
| Labeling sleeve side B | Yes | No. of torsion cycles | approx. 2000000 Cycles |
| Cables | | Paired stranding | No |
| Cable length | 2500 cm | Single wire diameter | 0.1 mm |
| Length tolerance | ± 37.5 cm | Cable: Test voltage | 2.5 kV |
| Shielded | No | Torsion stress in ° | $\pm 180^\circ/\text{m}$ |
| Conductor structure | 32 × 0.1 mm | Total stranding | 4 wires strand |
| AWG | 24 | Travel speed (C-track) | max. 3 m/s |
| External sheath: Material | PUR | Traversing path (horizontal) | max. 10 m |
| External sheath: Color | Black | Wire cross section | 0.25 mm ² |
| Cable diameter | 4.5 mm \pm 5% | Wire processing | No |
| Wire cross section | 0.25 mm ² | Wire diameter incl. isolation | 1.25 mm \pm 5% |
| Cable | | | |
| External sheath: Shore hardness | 90 \pm 5 A | | |

The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

Technical data

Cable

External sheath: Color Black

Electrical data

Operating voltage max. 50 V AC / 60 V DC

Operating voltage (only UL listed) 30 V AC/DC

Nominal voltage 300 V

Contact resistance max. 30 mOhm

Operating current per contact max. 4 A

Mechanical data

Head A: Degree of protection IP65, IP66K, IP67

Head B: Degree of protection IP65, IP66K, IP67

Bending radius (mobile) min. 10 × outer diameter

Bending radius (fixed) min. 5 × outer diameter

No. of bending cycles (C-track) approx. 10000000 Cycles

Torsion speed max. 35 cycles/min

Torsion stress in ° ± 180 °/m

No. of torsion cycles approx. 2000000 Cycles

Acceleration (C-track) max. 10 m/s²

Travel speed (C-track) max. 3 m/s

Environmental conditions

Temperature range (mobile) - 25 ...+ 80 °C

Temperature range (fixed) - 25 ...+ 80 °C

Environmental conditions

Cable: Temperature range (fixed) - 40 ...+ 80 °C

Dragchain capable Yes

Head A: Chemical resistance No

Head A: Flame resistance HB (UL 94)

Head A: Oil resistance ASTM 1 oil, mineral oils, limited to hydraulic oils

Head A: Acid and alkali resistant No

Head A: Pollution degree 3

Head B: Chemical resistance No

Head B: Flame resistance HB (UL 94)

Head B: Oil resistance ASTM 1 oil, mineral oils, limited to hydraulic oils

Head B: Acid and alkali resistant No

Head B: Pollution degree 3

Cable: Chemical resistance Good (DIN EN 60811-404)

Cable: Flame resistance Conform UL 1581 §1090 (H), CSA FT2, IEC 60332-2-2

Cable: Oil resistance Good (DIN EN 60811-404)


Cable: Silicone-free Yes

Commercial data

Eclass 27060311


Side A

Technical drawing



Side A

Coding



Side B

Technical drawing



Dimension drawing



Coding



Connection diagram

