

Vue d'ensemble

- IO-Link converter
- Single channel analog output multi
- 4...20 mA, 0...20 mA, 0...10 V, -10...10 V
- 16 bit resolution, <0,1% precision
- 2,3 ms cycle time



Caractéristiques techniques

Données générales

Degree of protection	IP67
LED Indicators	Module status IO-Link
Communication Interfaces	IO-Link
Software	Baumer Sensor Suite

Données électriques

Power supply	18 - 30 V DC
Power Consumption	230 mA

Interface de communication IO-Link

IO-Link port type	Class A
Short-circuit-proof	Oui
Reverse polarity protected	Oui

Données mécaniques

Model	Cubic
Enclosure	PC + PBT

Données mécaniques

Width	15 mm
Height	32,3 mm
Depth	77,2 mm
Weight	44 g

Conditions ambiantes

Operating temperature	- 30 °C ... + 70 °C
Storage temperature	- 40 °C ... + 85 °C

Sortie analogique

Input signal	4...20 mA
	0...20 mA
	0...10 V
	-10...10 V
Accuracy	4...20 mA: 0.1 %
	0...20 mA: 0.1 %
	0...10 V: 0.1 %
	-10...10 V: 0.1 %

Schéma de raccordement

