

GCA12 - SAE J1939


Interface SAE J1939

Measuring length absolute 10 m and 12 m

Preliminary

Overview

- Interface SAE J1939
- Redundant version
- Potentiometer sensing measuring method
- Operating temperature -40...+85 °C
- Protection IP 67
- Flange connector M12 or cable
- Measuring length 10 m and 12 m
- Designed for harsh environmental conditions
- Removable rubber plugs for drainage
- Load-dump protection
- Integrated inclination sensor



Technical data

Technical data - electrical ratings

Voltage supply	8...36 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes
Consumption typ.	30 mA (24 VDC, w/o load) 60 mA (24 VDC, w/o load, redundant)
Initializing time typ.	500 ms after power on
Interface	SAE J1939
Function	Linear position feedback
Measuring range	Up to 12 m (linear position) 360° (inclination angle)
Resolution	0.1 mm (linear position) 0.1 ° (inclination angle)
Temperature coefficient	0.04 °/K (inclination angle)
Linearity	±0.3 % FS (linear position) ±0.2° (inclination angle)
Absolute accuracy	±0.6 % FS (+25 °C / linear position) ±1.1 % FS (-40...+85 °C / linear position) ±0.3 ° (+25 °C / inclination angle)
Sensing method	Potentiometer
Code sequence	Programmable
Interference immunity	EN 61000-6-2
Emitted interference	EN 61000-6-3
Programmable parameters	Operating modes Rotating direction Scaling Zero position

Technical data - mechanical design


Protection EN 60529	IP 67 (electronic chamber) IP 54 (cable inlet)
Material	Cable: stainless steel cable AISI 316 coated with nylon PA12 Housing: plastic and aluminium
Operating temperature	-40...+85 °C
Measuring length	10 m 12 m
Cable diameter	0.7 mm
Cable fastening	Eyelet Height: 5 mm Internal diameter: 8 mm Outer diameter: 15 mm
Pull-in force	>2.5 N (pull-in force reduced at low temperatures)
Pull-out force	≤8 N (+25 °C)
Relative humidity	95 % non-condensing
Resistance	EN 60068-2-6 Vibration 20 g, 10-2000 Hz EN 60068-2-27 Shock 50 g, 11 ms
Weight approx.	1630 g
Connection	Flange connector M12, 5-pin Cable 2 m, radial
Instruction	Please consider the assembly instructions

Optional


- Integrated inclination sensor

Preliminary


Installation position




Position 1: 0/360°




Position 2: +90°



Position 3: +180°




Position 4: +270°



Terminal assignment

Flange connector M12, male, 5-pin, A-coded

Pin	Signals	Description
1	CAN_GND	Ground connection relating to CAN
2	+Vs	Voltage supply
3	GND	Ground connection relating to +Vs
4	CAN_H	CAN Bus Signal (dominant High)
5	CAN_L	CAN Bus Signal (dominant Low)



Cable

Core colour	Signals	Description
white	GND	Ground connection relating to +Vs
brown	+Vs	Voltage supply
green	CAN_H	CAN Bus Signal (dominant High)
yellow	CAN_L	CAN Bus Signal (dominant Low)
grey	CAN_GND	Ground connection relating to CAN

Cable data: 5 x 0.5 mm², 2 m

Terminals GND and CAN_GND are internally connected and identical in their functions.

SAE J1939 features

Programmable parameters	Rotating direction Scaling Zero position
Default	Baud rate 250 kbit/s Channel A: ECU address 4 (04h) Channel A: ECU address 5 (05h) Time-driven: 100 ms

GCA12 - SAE J1939

Interface SAE J1939

Measuring length absolute 10 m and 12 m

Preliminary

Data transfer

ECU address 4

PGN65363 – cyclic message (PDU2 format)

LSB	MSB
Byte 0	1	2	3	4	5	6	7
linear position 0 → 100000\120000 _{dec} in steps of 0.1 mm position increasing in size and value			Speed value		Status		

PGN65364 – cyclic message (PDU2 format)

LSB	MSB
Byte 0	1	2	3	4	5	6	7
inclination angle 0 → 3600 _{dec} in steps of 0.1° angle increasing in size and value							

ECU address 5

PGN65363 – cyclic message (PDU2 format)

LSB	MSB
Byte 0	1	2	3	4	5	6	7
linear position 0 → 100000\120000 _{dec} in steps of 0.1 mm position increasing in size and value			Speed value		Status		

PGN65364 – cyclic message (PDU2 format)

LSB	MSB
Byte 0	1	2	3	4	5	6	7
inclination angle 0 → 3600 _{dec} in steps of 0.1° angle increasing in size and value							



GCA12 - SAE J1939

Interface SAE J1939


Measuring length absolute 10 m and 12 m

Preliminary

Dimensions



GCA12 with cable




GCA12 - SAE J1939

Interface SAE J1939

Measuring length absolute 10 m and 12 m

Preliminary

Dimensions



GCA12 with flange connector (male) M12

GCA12 - SAE J1939

Interface SAE J1939

Measuring length absolute 10 m and 12 m

Preliminary

Ordering reference

	GCA12	-	P	P	###	.	R	C	#	.	##	0	.	A	.	#
Product	GCA12															
Type	Plastic			P												
Technology	Potentiometer			P												
Measuring range	10 m											100				
	12 m											120				
Measuring wire fixation	Ring							R								
Measuring wire diameter	0.70 mm							C								
Connection	Cable radial, 2 m															L
	Flange connector M12, 5-pin, radial, male contacts, CCW															N
Voltage supply / output	8...36 VDC, SAE J1939															CD
	8...36 VDC, SAE J1939 redundant (2-channel design)															CR
Resolution supplement	No option															0
Operating temperature	-40...+85 °C															A
Inclination sensor (axes / measuring range)	1-dimensional / 0...360°															
	Without inclination sensor															136