

CFAM 18N3600

Capacitive proximity sensors

Article number: 10119686

Overview

- 8 mm
- NPN break function (NC)
- potentiometer, 12 turn
- cable, 2 m
- -25 ... 75 °C
- IP 65



Picture similar



Technical data

General data

| | |
|--|-------------------------|
| Nominal sensing distance Sn | 8 mm |
| Nominal sensing distance Sn adjustable | 2 ... 8 mm |
| Mounting type | Flush |
| GND electrode | Yes |
| Temperature drift | ± 15 % (+10 ... +70 °C) |
| Sensitivity adjustment | Potentiometer, 12 turn |
| Output indicator | LED yellow |
| Measurement type | Contactless |

Field of application

| | |
|--|-----|
| Detection of non-conductive media | Yes |
| Fill level detection through container | Yes |
| Liquids in direct contact | No |
| Object detection / bulk goods | Yes |

Electrical data

| | |
|------------------------------------|-------------------------|
| Voltage supply range +Vs | 10 ... 30 VDC |
| Current consumption max. (no load) | 20 mA |
| Output circuit | NPN break function (NC) |
| Output current | < 200 mA |
| Voltage drop Vd | < 1.5 VDC |
| Switching frequency | 50 Hz |
| Short circuit protection | Yes |
| Reverse polarity protection | Yes |

Mechanical data


| | |
|------------------|----------------------|
| Type | Cylindrical threaded |
| Housing material | Brass nickel plated |
| Dimension | 18 mm |
| Housing length | 64 mm |
| Connection types | Cable, L=2 m |

Ambient conditions

| | |
|-----------------------|----------------|
| Operating temperature | -25 ... +75 °C |
| Protection class | IP 65 |

CFAM 18N3600

Dimension drawing



Connection diagram

