

Overview

- Outstanding reliability and unrivalled immunity against ambient light
- Baumer PinPoint LED: Small, homogeneous light spot with sharp edges
- Extra range - best-in-class
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Quick mounting by means of M3 threaded bushes made of stainless steel



Picture similar




Technical data


| General data | | Electrical data | |
|-------------------------------------|---------------------------|------------------------------------|---------------------------------------|
| Type | Background suppression | Current consumption max. (no load) | 40 mA (@ 10 VDC) |
| Sensing distance Tw | 20 ... 175 mm | Current consumption typ. | 16 mA (@ 24 VDC) |
| Sensing range Tb | 3 ... 192 mm | Voltage drop Vd | <2 VDC |
| Smallest object recognizable typ. | 1 mm at 100 mm | Output function | Light / dark operate |
| Power on indication | LED green | Output circuit | NPN complementary |
| Alignment / soiled lens indicator | Flashing output indicator | Output current | 50 mA |
| Output indicator | LED yellow | Short circuit protection | Yes |
| Sensing distance adjustment | qTeach | Reverse polarity protection | Yes |
| Suppression of reciprocal influence | Yes | Mechanical data | |
| Beam type | Point | Width / diameter | 8 mm |
| Alignment optical axis | < 1,5° | Height / length | 25.1 mm |
| Light Source | | Depth | 15.8 mm |
| Light source | Pulsed PinPoint LED | Design | Rectangular |
| Wave length | 644 nm | Mechanical mounting | Threaded sleeves M3 (stainless steel) |
| Electrical data | | Housing material | Plastic (ASA, PMMA) |
| Response time / release time | ≤ 0.5 ms | Front (optics) | PMMA |
| Jitter | ≤ 0.12 ms | Connection types | Cable 4 pin, 2 m |
| Voltage supply range +Vs | 10 ... 30 VDC | Cable characteristics | PVC / PVC 4 x 0.08 mm ² |
| | | Ambient conditions | |
| | | Protection class | IP 67 |
| | | Operating temperature | -25 ... +50 °C |

2024-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.


Dimension drawing




Hysteresis curve



Connection diagram



Beam characteristic (typically)



Sensing distance diagram

