

FUH 010B2002

Glass fiber optic cable

Article number: 10258981

Overview

- Diffuse type
- Sensing distance up to 25 mm
- Chrome-nickel sleeve $\varnothing 2$ mm
- Metal sleeve 10 cm long
- Operating temperature up to +120 °C
- For rugged fiber optic sensors FVDM 15



Picture similar

Technical data


General data

Operating principle	Diffuse type
Sensing distance T_w	25 mm
Fiber optic head	Cylindrical smooth
Operating temperature	-25 ... +120 °C
Exit angle	60°
Fiber optics can be shortened to length	No
Integrated lens	No
Adaptable lens	No
Infrared light compatibility (1450 nm)	Yes


Mechanical data

Width / diameter (head)	2 mm
Height / length (head)	100 mm
Material (head)	Chrome nickel steel
Bending radius (fixed)	0 mm
Cable jacket diameter	2 mm
Material cable jacket	Stainless steel
Fiber cross section	0.5 mm ²
Material (fiber optic cable)	Glass

Dimension drawing



Fiber arrangement



Accessories

Fitting fiber optic sensors

10234639	FVDM 15N5103
10122368	FVDM 15N5103/S14
10234520	FVDM 15P5103
10239451	FVDM 15P5103/S14
10234519	FVDM 15P5130
10124952	FVDM 15P5130/S14

Accessories

Mounting accessories

10103230	Replacement cap nut for fiber optics series 15
----------	--