

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable

### Overview

- Interface CANopen®
- Magnetic sensing method
- Resolution: singleturn 13 bit, multiturn 16 bit
- Function display via LEDs
- Multiturn sensing with Energy Harvesting technology "MicroGen", without gear or battery
- Two-sided bearing system with hybrid bearings
- Special protection against corrosion CX (C5-M)



Picture similar

HUBNER
BERLIN
A Baumer Brand

microGen Energy Harvesting

Technical data			
Technical data - electrical ratings		Technical data - electrical ratings (speed switch)	
Voltage supply	1030 VDC	Output switching capacity	30 VDC; ≤100 mA
Short-circuit proof	Yes	Switching delay time	≤20 ms
Consumption w/o load	≤200 mA	Technical data - mechanica	al design
Initializing time	≤ 500 ms after power on	Size (flange)	ø105 mm
Interface	CANopen®	Shaft type	ø1620 mm (blind hollow shaft)
Function	Multiturn		ø17 mm (cone shaft 1:10)
Transmission rate	10 1000 kBaud	Flange	Support plate, 360° freely positionable
Device adress	Rotary switches in bus connecting box	Protection EN 60529	IP 66/IP 67
Steps per revolution	8192 / 13 bit	Operating speed	≤6000 rpm
Number of revolutions	65536 / 16 bit	Range of switching speed	ns (off) = ±26000 rpm, factory setting 6000 rpm
Additional outputs	Square-wave TTL/HTL,TTL/RS422	Operating targue tun	10 Ncm
Sensing method	Magnetic	Operating torque typ.  Rotor moment of inertia	
Interference immunity	EN 61000-6-2		950 gcm²
Emitted interference	EN 61000-6-3	Admitted shaft load	≤450 N axial ≤650 N radial
Programming interface	RS485 (≤600 m)	Material	Housing: aluminium alloy
Programmable parameters	Bus system: see bus features		Shaft: stainless steel
	Additional output (number of pulses), switch-off and switch-on speeds	Corrosion protection	IEC 60068-2-52 Salt mist for ambient conditions CX (C5-M) accord-
Diagnostic function	Position or parameter error		ing to ISO 12944-2
Status indicator	DUO-LED (bus connecting box) 4 LEDs	Operating temperature	-40+85 °C
	in device back side	Relative humidity	95 % non-condensing
Approval	CE UL approval / E217823 EAC	Resistance	IEC 60068-2-6 Vibration 30 g, 10-2000 Hz IEC 60068-2-27
Technical data - electrical ratings (speed switch)			Shock 400 g, 1 ms
Switching accuracy	± 2 % (or 1 Digit)	Weight approx.	2.2 kg (depending on version)
Switching outputs	1 output (Open collector, solid state relay on request)	Connection	Bus connecting box Terminal box incremental

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable


### **Optional**

- Integrated speed switch programmable
- Additional output incremental programmable

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable

#### **Terminal assignment**

#### CANopen - View A (see dimension) View inside bus connecting box CANopen®



Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections UB-UB and GND-GND is 1 A each.


### Terminating resistor (1)

ON = Last user OFF = User x



### User address (2)

Defined by rotary switch. Example: User address 23



#### **CANopen - Transmission rate (3)**




Transmission rate	Setting DIP switches		
Transmission rate	1	2	3
10 kBaud	OFF	OFF	OFF
20 kBaud	OFF	OFF	ON
50 kBaud*	OFF	ON	OFF
125 kBaud	OFF	ON	ON
250 kBaud	ON	OFF	OFF
500 kBaud	ON	OFF	ON
800 kBaud	ON	ON	OFF
1000 kBaud	ON	ON	ON

<sup>\*</sup> Factory setting


#### **Terminal assignment**

#### CANopen - View A1 and A2 (see dimension)

View into connector



Connector M12 (male, A1) 5-pin, A-coded



Connector M12 (female, A2) 5-pin, A-coded


Pin	Connection
1	GND
2	UB
3	GND
4	CAN_H
5	CAN_L

Terminals of the same significance are internally connected and identical in their functions. Max. load on the internal terminal connections GND-GND is 1 A each.

### View B (see dimension)

Connecting terminal terminal box Programming interface / speed switch / additional output II (HTL, TTL)

\* Assignment depends on encoder version



### **Terminal significance**

#### **CANopen®**

Connection	Description
GND	Ground for UB
UB	Voltage supply 1030 VDC
CAN_H	CAN Bus signal (dominant HIGH)
CAN_L	CAN Bus signal (dominant LOW)

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable


Terminal significance	•
Ub	Voltage supply
0V	Ground
A+	Output signal channel 1
A-	Output signal channel 1 inverted
B+	Output signal channel 2 (offset by 90° to channel 1)
B-	Output signal channel 2 inverted
R+	Zero pulse (reference signal)
R-	Zero pulse inverted
nE+	System OK+ / error output
nE-	System OK- / error output inverted
SP+	DSL_OUT1 / speed switch (open collector, solid state relay on request)
SP-	DSL_OUT2 / speed switch (0V, solid state relay on request)
SA	RS485+ / programming interface
SB	RS485- / programming interface
dnu	Do not use

CANopen® features	
Bus protocol	CANopen®
Features	Device Class 2 CAN 2.0B
Device profile	CANopen® CiA DSP 406, V 3.0
Operating modes	<ul><li>Polling mode (asynch, via SDO)</li></ul>
	<ul><li>Cyclic mode (asynch-cyclic)</li></ul>
	<ul><li>Synch mode (synch-cyclic)</li></ul>
	<ul><li>Acyclic mode (synch-acyclic)</li></ul>
Diagnosis	The encoder supports the following error warnings:
	<ul><li>Position errror</li></ul>
Factory setting	User address 00

### **Output signals**

### Additional output II (HTL/TTL)

At positive rotating direction (see dimension)



### **Trigger level**


#### Incremental HTL/TTL

Electrically isolated:

The output TTL/HTL (Vin = Vout) at the additional output II is electrically isolated and requires a separate power supply.

Trigger level	TTL/RS422
High / Low	≥2.5 V / ≤0.5 V
Transmission length	≤550 m @ 100 kHz
Output frequency	≤600 kHz
Trigger level	TTL/HTL (Vin = Vout)
High / Low	≥2.5 V / ≤0.5 V (TTL) ≥Ub -3 V / ≤1.5 V (HTL)
Transmission length	≤550 m @ 100 kHz (TTL) ≤350 m @ 100 kHz (HTL)


### Switching characteristics speed switch



n	Speed
+ns (off)	Switch-off speed at shaft rotation in positive rotating direction (see dimension).
-ns (off)	Switch-off speed at shaft rotation in negative rotating direction (see dimension).
	Switching hysteresis
+ns (on)	Switch-on speed at shaft rotation in positive rotating direction (see dimension).
-ns (on)	Switch-on speed at shaft rotation in negative rotating direction (see dimension).

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable


# **Dimensions** 79.5 69.5 86.5 66.6 86.5 ø50 ød | L1 | L2 16 | 53 | 65.5 20 | 35 | 50




111.5

Blind hollow shaft with terminal box

Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable






Cone shaft with terminal box



Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable



- (1) Switching speed 6000 rpm / factory setting, programmable
- (2) Factory setting, programmable



Blind hollow shaft or cone shaft (1:10) / CANopen® / 13 bit ST / 16 bit MT Speed switch, number of pulses and switching speed freely programmable

Accessories	
Mounting access	ories
11043628	Torque arm M6, length 6770 mm
11004078	Torque arm M6, length 120130 mm (≥71 mm)
11002915	Torque arm M6, length 425460 mm (≥131 mm)
11054917	Torque arm M6 insulated, length 6770 mm
11072795	Torque arm M6 insulated, length 120130 mm (≥71 mm)
11082677	Torque arm M6 insulated, length 425460 mm (≥131 mm)
11077197	Mounting kit for torque arm size M6 and earthing strap
11077087	Mounting and dismounting set

### **Connectors and cables**

11191145 Programming cable for the HMG10P/PMG10P bus

interfaces series

### **Programming accessories**

11190106 Z-PA.SDL.1 - WLAN-Adapter