

**Overview**

- Reliable intensity-based object detection
- IO-Link interface independent of the switching output (Dual Channel)
- Extended parameterization options and additional diagnostic data
- Quick mounting by means of M3 threaded bushes made of stainless steel



Picture similar



**Technical data**

General data		Electrical data	
Type	Intensity difference	Reverse polarity protection	Yes
Version	IO-Link dual channel	Communication interface	
Sensing distance Tw	20 ... 200 mm	Interface	IO-Link V1.1
Smallest object recognizable typ.	2 mm at 100 mm	IO-Link port type	Class A
Power on indication	LED green	Baud rate	38,4 kBaud (COM 2)
Alignment / soiled lens indicator	Flashing output indicator	Cycle time	≥ 2.7 ms
Output indicator	LED yellow	Process data length	32 Bit
Sensing distance adjustment	IO-Link	Process data structure	Bit 0 = SSC1 (presence) Bit 2 = quality Bit 3 = alarm Bit 5 = SSC4 (counter) Bit 16-31 = 16 Bit measurement
Suppression of reciprocal influence	Yes	Adjustable parameters	Switching point Time filters LED status indicators Output logic Output circuit Counter Deactivate the sensor element Find Me function Teach-in mode
Beam type	Point	Additional data	Signal strength Excess gain Operating cycles Device temperature
Alignment optical axis	< 1,5°	Mechanical data	
Light Source		Width / diameter	8 mm
Light source	Pulsed red LED	Height / length	25.1 mm
Wave length	644 nm	Depth	15.8 mm
Electrical data		Design	Rectangular
Response time / release time	< 0.4 ms	Mechanical mounting	Threaded sleeves M3 (stainless steel)
Jitter	< 0.21 ms	Housing material	Plastic (ASA, PMMA)
Voltage supply range +Vs	10 ... 30 VDC		
Current consumption max. (no load)	45 mA (@ 10 VDC)		
Current consumption typ.	16 mA (@ 24 VDC)		
Voltage drop Vd	<2 VDC		
Output function	Light / dark operate		
Output circuit	Push-pull		
Output current	50 mA		
Short circuit protection	Yes		

2024-02-16 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

**Technical data**


**Mechanical data**

Front (optics)	PMMA
Connection types	Flylead connector M8 4 pin, L=200 mm
Cable characteristics	PVC / PVC 4 x 0.08 mm <sup>2</sup>


**Ambient conditions**

Protection class	IP 67
Operating temperature	-25 ... +50 °C


**Dimension drawing**




**Relative receiving signal**



**Connection diagram**



**Pin assignment**



**Beam characteristic (typically)**

