

Overview

- Intuitive OLED display
- Programmable input configurations
- Crosstalk rejection between two sensors without a wire
- Six AUTOSSET modes
- Advanced remote programming



Picture similar



Technical data

General data

Light source	Pulsed red LED
Light indicator	OLED display
Output indicator	LED red
Adjustment	Teach-in: button / external
Wave length	660 nm
Suppression of reciprocal influence	Yes

Electrical data

Response time / release time	0.05 ms (Ultra High Speed Mode) 0.125 ms (High Speed Mode) 0.25 ms (Standard Mode) 1 ms (High Resolution Mode) 4 ms (Long Range Mode) 16 ms (Ultra Long Range Mode)
Voltage supply range +Vs	8 ... 30 VDC
Current consumption max. (no load)	50 mA
Current consumption typ.	30 mA

Electrical data

Voltage drop Vd	<2 VDC
Output function	Light / dark operate switchable
On / off delay	0.1 ... 9999 ms
Output circuit	NPN
Output current	150 mA
Short circuit protection	Yes
Reverse polarity protection	Yes


Mechanical data

Width / diameter	10 mm
Height / length	27.8 mm
Depth	82.3 mm
Design	Rectangular
Housing material	Polycarbonate
Connection types	Cable 4 pin, 2 m

Ambient conditions

Operating temperature	5 ... +55 °C
Protection class	IP 50

Dimension drawing



Connection diagram



Accessories

Mounting accessories

11708560	ZADAP-FBR.BRACKET
----------	-------------------